



## Dry Box



Heat drying + UV



Environmentally friendly

# Drying box for hearing aids with built-in battery tester

#### **Functions:**

- Removes moisture and condensation via gentle heat drying with simultaneous UV light radiation with 3 selectable levels
- Removable plastic shell (dishwasher safe)
- Environmentally-friendly you do not need any expensive chemicals or drying agents
- 4 powerful UV lights ensure for even radiation
- UV light inhibits the growth of bacteria which can cause itchy ears
- Integrated battery tester testing the batteries prevents premature replacement and helps you save money.
- The device is easy to open, even for people with arthritis with auto-stop function if the cover is opened during operation.
- Easy single-button operation
- Drying cycle timer 2 / 4 / 8 hours
- Can hold up to 2 pairs of hearing aids or cochlear implants.

#### **Technical specifications:**

- Power adapter AC input 100-240V, DC output 12V 1A
- Compartment temperature : 45° C +/- 5° C

### Dimensions (width x depth x height):

drybox : 215 x 130 x 45 mm
Giftbox : 258 x 175 x 120 mm

Inner box : 370 x 270 x 265 mm -- 4pcs gift box per one inner box

Master carton: 552 x 389 x 555 mm -- 16pcs gift box per one master carton



Content







Warranty: 24 months

EAN No.: 4250711 906511 Order No.: 906511

Export Carton: 16 pcs with EAN Barcode

Picture similar / technical data / features and design are subject to permanent technical development and could be changed without prior notice – errors accepted.

AUDIOLINE GMBH - Hellersbergstr. 2a D-41460 Neuss

Phone: +49 2131 / 79 90-0 Sales: +49 2131 / 79 90-10 Fax: +49 2131 / 27 69 90